



# PBC-7

## CALL CORD w/PHONE PLUG



**UL 1069 and CSA C22.2#205  
5002971**



### BENEFITS

- High Impact Thermoplastic
- Durable 7 Foot Cord
- Easy to Install
- Easy to Operate
- Right Angel Phone Plug

The Tech Works **PBC-7** is a Push Button Call Cord made of high impact thermoplastic with a 7-foot cord and right angle 1/4 inch phone plug. Designed to provide remote push button operation from the **NC-PBS-1** Emergency Push Button Station or the **PBS** generic patient bed station by simply plugging it into the jack. The button is a non-locking normally open contact passive assembly designed for use with Intelligent Substations listed above. The cord set comes with a security clip and is completely shock and waterproof for use in sterile environments.

This device has been tested and is proven safe in oxygen rich environments.

### Associated Equipment

- |                 |                               |
|-----------------|-------------------------------|
| <b>NC-PBS-1</b> | NC-Series Patient Bed Station |
| <b>NC-PCBS</b>  | Patient Bed Station           |

### Design Information

- |                   |  |
|-------------------|--|
| <b>Power</b>      | N/A                                      |
| <b>Color</b>      | White                                    |
| <b>Mounting</b>   | 1/4" Phone Jack                          |
| <b>Dimensions</b> | <b>Housing</b> - 2.375" L x 1.0" W       |
|                   | <b>Cord</b> - 0.25" Dia. x 7' L x 18 AWG |
|                   | <b>Plug</b> - 0.25" Dia. x 1.8" x 1.6" H |

### Architects' and Engineers' Specifications

The Light Signaling System Call Cord shall be a standard normally open contact device constructed of thermoplastic and shall include a 1/4 inch phone plug for quick connect to wall mounted Stations. The Push Button shall be a momentary non-locking assembly in a 2.375" long by 1.0" wide housing. The cord assembly shall be 0.25" in diameter with a plastic jacket and measure at least 7 feet in length. The device shall include a molded right angle 1/4 inch phone plug for connection to the signaling system and a security clip for attachment to patient furniture. The Light Signaling System Room Status Call Cord shall be Tech Works Model PBC-7



# Tech Works®

"Making Specialized Communication Easy"