



# NC-VP-CS

## Nurse Call Vandal Proof Cancel only Station



UL 1069 and CSA C22.2#205  
5002971

The Tech Works **NC-VP-CS** is a Cancel only Station with a Vandal Resistant Push button with concentric Call Assurance Light built in to the button and mounted on a rugged stainless-steel plate. This station is intended to be used with our other NC-Series products when a Remote Cancel only button is required to reset a dome light. Staff is provided with a distinctive "CANCEL" button to reset other station.

An integral call confirmation LED notifies the user that a call for help has been sent. The Call Assurance Light will be Off if no call is pending, glowing steadily if a Normal Call is pending, and flashing if a Call is Pending.

This is a passive button-and-light assembly designed for use with active stations like the **NC-DL-12** Dome Light. Screw Terminals provide wiring connection to the active electronic stations that provide signaling and control for the **NC-VP-CS**.

Mounting is a standard 1-gang electrical box. The Face Plate is made of 12-gauge Stainless Steel with a brushed finished and includes tamper resistant mounting screws.

### BENEFITS

- Reliable Signaling
- No Maintenance
- Low Power
- Simple Wiring
- Easily Integrates to other Systems

### Associated Equipment

<b>NC-DL-12</b>	Dome Light
<b>NC-VP-SAS</b>	Staff Assist Station
<b>NC-VP-PBS</b>	Patient Bed Station
<b>VPBL-1</b>	Push Button

### Design Information

<b>Power</b>	15V DC
<b>Color</b>	Stainless Steel
<b>Mounting</b>	1 Gang Back Box
<b>Dimensions</b>	3.25" W x 0.5" D x 5" H
<b>Weight</b>	0.25 lbs.

### Architects' and Engineers' Specifications

The Nurse Call System Cancel only Station shall be a standard one gang electrical box mounting device constructed of Vandal Resistant Stainless Steel. A distinctive Cancel button shall be provided to reset the station. A call confirmation light shall be included to indicate that a call has been placed. The Cancel station shall be a passive electronic device requiring no more than 3 mA at 15 Volts DC for full operation.

The Nurse Call System Cancel only Station shall be Tech Works Model NC-VP-CS.



# Tech Works®

"Making Specialized Communication Easy"

