



CI-Series Technical Training Test Part 2 – Parts & Pieces

Your Name: First: _____ Last: _____

Contact Information: Email: _____

Company/Employer: _____ Phone: _____

1. Why is the CI-Series called a Collaboration Intercom?
 - a. It has Audio and Visual Collaboration components
 - b. There are a variety of Audio Interfaces that can Collaborate over CAT6 Cabling
 - c. Designed for internet collaboration like meetings
 - d. None of the above
2. CI-Series is modular which allows:
 - a. Each interface to contain the functionality for different parts of a system application
 - b. Each interface to contain the circuitry to support different parts of a system application
 - c. You to buy only the pieces you need to built your application
 - d. All of the above
3. The CI-ODC-1 is:
 - a. Complete standalone system
 - b. Complete Operator Desk Console
 - c. Just a box with a Microphone and Speaker
 - d. All of the above
4. A CI-ODC-4 can:
 - a. Talk to up to 4 remote systems
 - b. Has a built-in headset interface
 - c. Can be used Handsfree or Push to Talk
 - d. All of the above
5. A CI-MSI-22:
 - a. Is required for every system
 - b. Has a built-in 25 Volt Audio Power Amplifier
 - c. Has a built-in professional Microphone Input
 - d. Both b and c above
6. The CI-MSI-22 has the ability to:
 - a. Route the buss audio from one device to another
 - b. Duck back ground music
 - c. Signal an Operator that the procedure room needs attention
 - d. All of the above



CI-Series Technical Training Test Part 2 – Parts & Pieces

7. The CI-HSI-41:
 - a. Can combine 4 headsets to talk to each other
 - b. Can make one headset the "Chairman" and 3 others listeners
 - c. Can be connected to additional CI-HSI-41 if more headset are needed
 - d. All of the above
8. Does the CI-HSI-41 have a PA-BUSS connection to PA Amplifiers?
 - a. Yes
 - b. No
9. Does the CI-HSI-41 have a Call contact input to signal an operator that someone needs attention?
 - a. Yes
 - b. No
10. In a CI-Series system, what is a PA-402 used for?
 - a. Background music
 - b. Paging
 - c. Remote listening and observation
 - d. All of the above
11. What are the mounting options for CI-Series products?
 - a. Rack Mount
 - b. Wall Mount
 - c. Desk Mount
 - d. Side by Side
 - e. All of the above
12. How many types of foot switches are available for the CI-Series?
 - a. One
 - b. Two
 - c. Three
 - d. Four



CI-Series Technical Training Test Part 2 – Parts & Pieces

13. Headsets that work with the CI-Series are:
 - a. Wired headsets
 - b. Bluetooth Headsets
 - c. Any old headset
 - d. Plantronics (Poly) wireless headsets
14. CI-Series microphone options include:
 - a. PRO-42 Boundary Microphone - Boom Arm Applications
 - b. PRO-45 Hanging Microphone - Ceiling Mount Applications
 - c. PRO-SGM Shotgun Microphone - Wall Mount Applications
 - d. Hidden Microphones
 - e. All of the above
15. CI-Series speakers are:
 - a. Clean Room rated
 - b. Ceiling Mount
 - c. Wall Mount
 - d. All of the above
16. What is not an option available with the CI-Series?
 - a. A one-watt amplifier
 - b. CAT6 patch cord
 - c. Power Cords
 - d. Text Messaging
17. What powers the CI-Series?
 - a. 24 VDC
 - b. 12 VDC
 - c. None of the above
 - d. All of the above
18. How is the best way to get help with design assistance?
 - a. Call with little or no idea what you want or need
 - b. Call Sales and ask if we have everything in stock
 - c. Go to the web site and watch a video while reviewing the System Guide, then send us an email with as much information as possible (drawings, part numbers, scope of work, etc.)

If this button does not work please save your test and email it to info@TechWorks-USA.com